




Carriage bolt DIN 603 Stainless steel A4 70 M5X20

Article number	55500.050.020
Brand	-
UBB	951351838382
UNSPSC	31161612
EAN	8715492346285
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M5
Length	20 mm
Threaded pitch (P)	0.8
Class	70
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread

Standards

DIN	603
BS	≈4933
ISO	≈8677
NEN	≈303

Technical Specification

b (min.): 125mmL≤200mm	22
b (min.): L≤125mm	16
d-D	M5
dk (max.)	13.55
k (max.)	3.3
L (mm)	20
P	0.8
fn (max.)	4.1
Vn (max.)	5.48

Technical Drawing

