



Taper pin, turned DIN 1 B Stainless steel A5 (1.4571) 5X30MM

Article number	55560.050.030
Brand	-
UBB	500696133676
UNSPSC	31163205
EAN	8715492073242
PKG. of 100	Full Box Only

Technical Parameters

Length	30 mm
Material	Stainless steel
Material technical	A5 (1.4571)

Standards

DIN	1-B
ISO	≈2339-B

Info

Taper pins are designed for the friction type fastening and/or locking together of two or more individual elements. The tapered shape allows the connection to be disconnected repeatedly, and when the elements are joined together again, their location remains as accurate as it was previously, and the frictional connection remains as strong as before. The nominal length (L, tolerance class js15) does not include the rounded ends. For taper pins with $d1 = 20$ distance W is at the choice of the user.

Technical Specification

c (max.)	0.75
d1	5
d2	17
d2 ≤	23
L (mm)	30
r ≈	5
W (min.)	7.5

Technical Drawing

