



T-head bolt type 28/15
Stainless steel A4 M10X30

Article number	55740.100.030
Brand	-
UBB	500634383326
UNSPSC	31162400
EAN	8715494634472
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Length	30 mm
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

Technical Specification

b1	10
b2	22.5
d-D	M10
k	4.5
L (mm)	30

Technical Drawing

