



Threaded rod Permaglas
Glass Fibre Reinforced
Plastic ME 771 M10X950

Article number	56050.100.950
Brand	-
UBB	951353175353
UNSPSC	31161618
EAN	8715492860002
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M10
Length	950 mm
Color	Red
Material	Glass-fibre reinforced plastic
Material technical	Permaglas ME 771
Thread direction	Right
Thread	Metric thread

Info	Special features PERMAGLAS ME 771:Glass-fiber reinforced epoxy Temperature resistant – 270°C up to +155°C Light weight (density 1,9-2,0 g/cm³) Corrosion resistant, highly UV- and weather resistant Resistant to aggressive chemicals and gases Provides electrical and thermal insulation Non-magnetic Better mechanical
------	---

Standards

properties than e.g.
Polyamide

FABORY

Technical Specification

d-D	M10
L (mm)	950
P	1.5

Technical Drawing

