



Glass-fiber reinforced epoxy
Permaglas ME 730 M10

Article number	56054.100.001
Brand	-
UBB	950356547899
UNSPSC	31161807
EAN	8715492860132
PKG. of 8	Full Box Only

Technical Parameters

Diameter	M10
Color	Beige
For nom. size	10mm
Material	Glass-fiber reinforced epoxy
Material technical	Permaglas ME 730

Info	Special features PERMAGLAS ME 730:Glass-fiber reinforced epoxy Temperature resistant -270°C up to +155°C Light weight (density 1,85 g/cm³) Corrosion resistant, highly UV- and weather resistant Resistant to aggressive chemicals and gases Provides electrical and thermal insulation Non-magnetic Better mechanical properties than e.g. Polyamide
------	--

Standards

Technical Specification

d-D	M10
d1	11
d2	22
s	2

Technical Drawing

