

Hexagon head bolt DIN ≈931 Plastic Polyamide (nylon) 6.6 M12X40/30

Article number	56090.120.040
Brand	-
UBB	952351070265
UNSPSC	31161620
EAN	8715492860255
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M12
Length	40 mm
Class	6.6
Color	White
Driving features	Hexagon
Head shape	Hexagon head
Material	Plastic
Material technical	Polyamide (nylon)
Thread direction	Right
Thread	Metric thread

Standards

ASME	≈B18.2.3.1M
DIN	≈931
ISO	≈4014
NEN	≈1555
NF	≈E25-112

Technical Specification

b	30
b (min.): 125mmL≤200mm	36
b (min.): L200mm	49
b (min.): L≤125mm	30
d-D	M12
k	7.5
L (mm)	40
P	1.75
s	19

Technical Drawing

