



Slotted pan head screw DIN 85 Plastic Polyamide (nylon) 6.6 M3X20

Article number	56420.030.020
Brand	-
UBB	950353322387
UNSPSC	31161504
EAN	8715492863126
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3
Length	20 mm
Class	6.6
Color	White
Driving features	Slotted
Head shape	Pan head
Material	Plastic
Material technical	Polyamide (nylon)
Thread	Metric thread

Standards

NF	≈E25-128
ISO	≈1580
BS	≈4183
NEN	≈1603
ASME	≈B18.6.7M
DIN	85

Technical Specification

d-D	M3
Thread length (min.)	25
dk (max.)	6
Full thread if L ≤	30
k (max.)	1.8
L (mm)	20
n	0.8
P	0.5
t (min.)	0.7

Technical Drawing

