



KIPP Clamping levers, external thread Red Die cast zinc/steel 5.8 Plastic coated/ black oxide M10X65X45

Article number	58044.100.045
Brand	-
UBB	500689552239
UNSPSC	31162807
EAN	4059245091003
PKG. of 5	Full Box Only

Technical Parameters

Class	5.8
Color	Red
D1_MM	18.5mm
Material	Die cast zinc/steel
Surface treatment	Plastic coated/black oxide
Thread	Metric thread
Info	Material: Handle die-cast zinc EN 12844. Steel parts grade 5.8. Version: Handle plastic coated. Steel parts black oxidized. Drawing reference: 1) flat point DIN 78.

Standards

Technical Specification

A	65
A1	74.5
B	9.5
D	13.5
D1	18.5
D2	19
H	28.5

Technical Drawing

H2	17.5
H3	42.5
H4	45.5
H1	6.5
Number of teeth	20
L	45
X	10

