



**KIPP Clamping levers,
external thread Chrome
Die cast zinc/steel 5.8 High
gloss chromed/black oxide
M10X95X90**

Article number	58048.102.090
Brand	-
UBB	500689583911
UNSPSC	31162807
EAN	4059245092932
PKG. of 4	Full Box Only

Technical Parameters

Class	5.8
Color	Chrome
D1_MM	27mm
Material	Die cast zinc/steel
Surface treatment	High gloss chromed/ black oxide
Thread	Metric thread
Info	Material: Handle die- cast zinc EN 12844. Steel parts grade 5.8.Version: Handle high-gloss chromed. Steel parts black oxidized.Drawing reference: 1) flat point DIN 78.

Standards

Technical Specification

A	95
A1	109
B	13
D	19
D1	27
D2	27.5

Technical Drawing

H	43
H2	27
H3	63
H4	67.5
H1	10
Number of teeth	24
L	90
X	10

