



KIPP Clamping levers, external thread with cap Orange Die cast zinc/steel 5.8 Plastic coated/black oxide M6X65X55

Article number	58052.060.055
Brand	-
UBB	500689594074
UNSPSC	31162807
EAN	4059245094820
PKG. of 5	Full Box Only

Technical Parameters

Class	5.8
Color	Orange
D1_MM	18.5mm
Material	Die cast zinc/steel
Surface treatment	Plastic coated/black oxide
Thread	Metric thread
Info	Material: Handle die-cast zinc EN 12844. Steel parts grade 5.8. Protective cap stainless steel 1.4305. Version: Handle plastic coated. Steel parts black oxidized. Protective cap stainless steel, bright.

Standards

Technical Specification

A	65
A1	74.5
B	9.5
D	13.5

Technical Drawing

D1	18.5
D2	19
H	32
H2	17.5
H3	42.5
H4	45.5
H1	6.5
Number of teeth	20
L	55
X	6

