



KIPP Clamping levers, external thread Chrome Die cast zinc/stainless steel 1.4305 High gloss chromed/ bright M5X30X25

Article number	58062.050.025
Brand	-
UBB	500689629979
UNSPSC	31162807
EAN	4059245096039
PKG. of 4	Full Box Only

Technical Parameters

Color	Chrome
D1_MM	13mm
Material	Die cast zinc/ stainless steel
Material technical	1.4305
Surface treatment	High gloss chromed/ bright
Thread	Metric thread
Info	Material: Handle die- cast zinc EN 12844. Steel parts stainless steel 1.4305.Version: Handle high-gloss chromed. Steel parts bright.Drawing reference: 1) flat point DIN 78.

Standards

Technical Specification

A	30
A1	37
B	7
D	10
D1	13

Technical Drawing

D2	14
H	24.5
H2	14.5
H3	30
H4	33
H1	4
Number of teeth	16
L	25
X	5

