



**KIPP Clamping levers plastic grip, external thread Orange
Stainless steel 1.4305/plastic
M6X40X30**

Article number	58106.060.030
Brand	-
UBB	500689756764
UNSPSC	31162807
EAN	4059245110698
PKG. of 5	Full Box Only

Technical Parameters

Color	Orange
D1_MM	13mm
Material	Stainless steel/ plastic
Material technical	1.4305
Thread	Metric thread

Info	For many people the Novo-Grip clamping lever represents the key to secure and comfortable gripping. This lever provides a future-oriented and powerful solution for almost any operating and clamping problem. Material: Handle fibreglass reinforced plastic with die-cast zinc toothed ring. Steel parts stainless steel 1.4305. Version: Steel parts bright.
------	---

Standards

Technical Specification

A	40
A1	47

Technical Drawing

B	7.5
D	10
D1	13
D2	14.5
H	24.5
H2	15
H3	30
H4	33.5
H1	4
Number of teeth	16
L	30
X	6

