



Spring plungers with slot and thrust pin, LONG-LOK secured light spring force Steel 5.8 Black oxide M12

Article number 58533.120.001

Brand -

UBB 500689837200

UNSPSC 31162807

EAN

PKG. of 5 Full Box Only

Technical Parameters

Class	5.8
D1_MM	6mm
Driving features	Slotted
Material	Steel
Surface treatment	Black Oxide
Thread	Metric thread
Info	Material: Sleeve steel grade 5.8. Thrust pin steel. Spring steel grade D. LONG-LOK thread lock nylon. Version: Black oxidized. Thrust pin hardened. L2 = approx. 2x thread pitch.

Standards

Technical Specification

D	12
D1	6
F1 = springiness beginning in N	14
F2 = springiness end in N	26
H	3.5
L1	10

Technical Drawing

Loosening torque approx. (Nm)	1.41
N	2
L	22
Tightening torque approx. (Nm)	2.11

