



**KIPP Indexing plungers,
high, lockout type, without
locknut Metric fine thread
Stainless steel 1.4305, pin
not hardened, plastic grip
6MM**

| | |
|----------------|---------------|
| Article number | 58585.000.006 |
| Brand | - |
| UBB | 500689869211 |
| UNSPSC | 31162807 |
| EAN | 4059245013548 |
| PKG. of 3 | Full Box Only |

Technical Parameters

| | |
|--------------------|--|
| D1_MM | 12mm |
| Material | Stainless steel |
| Material technical | 1.4305 |
| Thread | Metric fine thread |
| Info | Material: Stainless steel. Threaded sleeve 1.4305 Indexing pin 1.4305 Mushroom knob black grey thermoplastic.Version: Indexing pin not hardened, ground and bright.Note: Indexing plungers are used to prevent any change in locking position due to lateral forces. A new locking position can only be set after the pin has been manually disengaged. The lockout types are recommended for applications in |

Standards

which the pin is disengaged over extended periods and should be prevented from springing back..

Technical Specification

| | |
|---------------------------------|-----|
| D | 6 |
| D1 | 12 |
| D2 | 25 |
| F1 = springiness beginning in N | 6 |
| F2 = springiness end in N | 14 |
| F x 30° | 1.8 |
| H | 6 |
| L1 | 20 |
| L2 | 8 |
| L3 | 17 |
| L | 56 |
| P | 1.5 |
| SW1 | 14 |

Technical Drawing

