



**KIPP Indexing plungers
with threaded pin, with
locknut Metric fine thread
Stainless steel 1.4305, pin
not hardened 10MM**

Article number	58593.000.010
Brand	-
UBB	500689874997
UNSPSC	31162807
EAN	4059245014200
PKG. of 1	Full Box Only

Technical Parameters

D1_MM	20mm
Material	Stainless steel
Material technical	1.4305
Thread	Metric fine thread

Info	Material: Stainless steel. Threaded sleeve 1.4305. Indexing pin 1.4305.Version: Indexing pin not hardened, ground and bright.Note: Indexing plungers are used to prevent any change in locking position due to lateral forces. A new locking position can only be set after the pin has been disengaged. Special grips can be fitted on the projecting threaded pin. This pin is also suitable for automatic actuation e.g. program controlled
------	--

Standards

pneumatic cylinder
or by remote control
using Bowden
cables.

Technical Specification

D	10
D1	20
D2	8
F1 = springiness beginning in N	15
F2 = springiness end in N	34
F x 30°	2.8
H	10
L1	28
L2	12
L3	12
L4	25
L	62
P	1.5
SW1	22
SW2	30

Technical Drawing

