



KIPP Precision indexing plungers with tapered pin, lockable Steel, grip ball thermoplastic black/grey 10MM

Article number	58643.000.010
Brand	-
UBB	500689906831
UNSPSC	31162807
EAN	4059245021406
PKG. of 1	Full Box Only

Technical Parameters

D1_MM	25mm
Material	Steel
Info	Material: Steel. Grip ball thermoplastic.Version: Hardened and ground. Grip ball black grey.Note: The indexing plungers with bushes are a perfect combination for rapid positioning and fixing. The precise design of both the indexing plunger and the bush guarantees high repeating accuracy when assembling two elements. Technical information see assembly and installation instructions.

Standards

Technical Specification

D	10
---	----

Technical Drawing

D1 25

D2 19

D3 16

F1 = springiness
beginning in N 19

F2 = springiness end
in N 29

L1 25

L2 32.5

L3 13

L4 6

L5 2.5

L 31

