



KIPP Precision indexing plungers with tapered pin, lockable Steel, grip ball thermoplastic black/grey 12MM

Article number	58643.000.012
Brand	-
UBB	500689906914
UNSPSC	31162807
EAN	4059245021413
PKG. of 1	Full Box Only

Technical Parameters

D1_MM	32mm
Material	Steel
Info	Material: Steel. Grip ball thermoplastic. Version: Hardened and ground. Grip ball black grey. Note: The indexing plungers with bushes are a perfect combination for rapid positioning and fixing. The precise design of both the indexing plunger and the bush guarantees high repeating accuracy when assembling two elements. Technical information see assembly and installation instructions.

Standards

Technical Specification

D	12
---	----

Technical Drawing

D1	32
D2	23
D3	20
F1 = springiness beginning in N	22
F2 = springiness end in N	35
L1	33
L2	40.5
L3	13
L4	6
L5	3
L	35

