



KIPP Precision indexing plungers with tapered pin, lockable Steel, grip ball thermoplastic black/grey 20MM

Article number	58643.000.020
Brand	-
UBB	500689907177
UNSPSC	31162807
EAN	4059245021437
PKG. of 1	Full Box Only

Technical Parameters

D1_MM	40mm
Material	Steel
Info	Material: Steel. Grip ball thermoplastic.Version: Hardened and ground. Grip ball black grey.Note: The indexing plungers with bushes are a perfect combination for rapid positioning and fixing. The precise design of both the indexing plunger and the bush guarantees high repeating accuracy when assembling two elements. Technical information see assembly and installation instructions.

Standards

Technical Specification

D	20
---	----

Technical Drawing

D1	40
D2	33
D3	30
F1 = springiness beginning in N	46
F2 = springiness end in N	63
L1	41.5
L2	49
L3	13
L4	6
L5	3
L	50

