



**KIPP Indexing plungers,  
non-lockout type, without  
locknut Metric fine thread  
Stainless steel 1.4305, pin  
not hardened, stainless steel  
grip 6MM**

Article number	58684.000.006
Brand	-
UBB	500690013577
UNSPSC	31162807
EAN	4059245010561
PKG. of 2	Full Box Only

Technical Parameters

D1_MM	12mm
Material	Stainless steel
Material technical	1.4305
Thread	Metric fine thread
Info	Material: Stainless steel. Threaded sleeve 1.4305. Indexing pin 1.4305. Mushroom knob 1.4305, electrolytic-polish. Version: Bright. Indexing pin not hardened, ground. Note: Indexing plungers are used to prevent any change in locking position due to lateral forces. A new locking position can only be set after the pin has been manually disengaged.

Standards

D	6
D1	12
D2	25
F1 = springiness beginning in N	6
F2 = springiness end in N	14
F x 30°	1.8
H	6
L1	20
L2	8
L3	17
L	59
P	1.5
SW1	14

