

Dormer Jobber drill A002
DIN 338 HSS Blanc/TiN
5.20mm



Article number	5J367606
Brand	-
UBB	500631001228
UNSPSC	23241639
EAN	7320760350850
PKG. of 10	Full Box Only

Technical Parameters

Total length	86
Diameter drill	5.2
Holding system	Cylindrical plug-in axle
Cutting length	52
Cutting material	HSS
Tip angle	118
Shank shape	Cylindrical
Spiral drill	Yes

Standards