



Brady Icon W003-TRI 315-PE

Article number	5Q973342
Brand	-
UBB	500671793791
UNSPSC	46180000
EAN	
PKG. of 1	Full Box Only

Technical Parameters

Color	Black/Yellow
Width (mm)	315
Adhesive component	Permanent Acrylic
Basic material	Laminated Polyester
Brady material number	B-7541
Country	EMEA
Legend	ISO Safety Sign - Warning; Radioactive material or ionizing radiation
Legend language	Global
Max. service temp. °C	110 °C
Min. service temp. °C	-40 °C
PIC description	Warning; Radioactive material or ionizing radiation
Product regulations	ISO 7010
Sign type	Warning
Content (pcs)	1
Number of holes	0
Finish	Gloss
Finish	Glanz
Finish	luciu

Standards

Finish	Połysk
Finish	Brillo
Finish	Lesk
Finish	Glanzend
Finish	Glossza
Finish	Gloss
Finish	lesk
Application method	Facility & safety identification
Height (mm)	273
Length (L) (mm)	315
Thickness	0.099
Type nr.	B-7541
Weight (g)	16
Shape	Triangle