



FISCHER Hammerset anchor Stainless steel A4 EA II M12 A4

Article number	63321.120.001
Brand	-
UBB	500504265710
UNSPSC	31162101
EAN	4006209484159
PKG. of 25	Full Box Only

Technical Parameters

Material	Stainless steel
Approval	ETA Option 7
Thread	Metric thread
Type no.	EA II

Standards

Info	do = Nominal diameter of drill bit. t = Recommended drilling depth. L (hef) = Effective anchorage depth. lsmin. = Screw-in depth min. lsmax. = Screw-in depth max. kN = Load in kN in combination with 8.8 & A4-70 bolts. Tinst = Tightening torque in Nm. The cone must be installed with setting tool type EAW H (narrow end) into the anchor body (article group 63322). Only part of the approval for light suspended ceilings. For further technical data the
------	---

approval is available
on request.

FABORY

Technical Specification

d-D	M12
d _o	15
h _{ef}	50
kN	8.5
L (mm)	50
l _s (max.)	22
l _s (min.)	12
t	54
T _{inst}	35
Type	EA II M12 A4

Technical Drawing

