



FISCHER Anchor bolt Steel Zinc plated FAZII12/200

Article number	63323.120.200
Brand	-
UBB	500504262337
UNSPSC	31162101
EAN	4006209956052
PKG. of 10	Full Box Only

Technical Parameters

Material	Steel
Approval	ETA Option 1
Surface treatment	Zinc plated
Thread	Metric thread
Type no.	FAZ II

Info

do= Nominal diameter of drill bit.Min. td= Recommended drilling depth.hef= Effective anchorage depth.tfix= Grip range.s = Width across flats.kN = Load in kN.The allowable load is valid for one single anchor, at cracked concrete (tensile zone) with concrete class C20/25, incl. partial safety factor $\gamma_f = 1,4$ and if the Scr, N and Ccr, N are taken in to account.Final calculations should comply with the complete European Technical Approval (ETA), this approval

Standards

is also available on
request.

FABORY

Technical Specification

d-D	M12
do	12
hef	70
kN	7.6
L (mm)	300
Min. td	295
Ring ø	24
s	19
tfix	200
Type	FAZII12/200

Technical Drawing

