



FISCHER Bolt type FBN II Steel Zinc plated 6/10 (6X55)

Article number	63324.060.010
Brand	-
UBB	500504267047
UNSPSC	31162101
EAN	4048962070248
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M6
Length	55 mm
Material	Steel
Approval	ETA Option 7
Surface treatment	Zinc plated
Thread	Metric thread
Type no.	FBN II

Info

do = Nominal diameter of drill
 bit.tfix = Grip
 range.hef = Effective anchorage depth.Min. td = Recommended drilling depth.kN = Load in kN.The allowable load is valid for one single anchor, at cracked concrete (tensile zone) with concrete class C20/25, incl. partial safety factor $\gamma_f = 1,4$ and if the Scr, N and Ccr, N are taken in to account.When reduction on spacing and edge distance take place a re-calculation of forces

Standards

should be carried out by making use of the technical guide or calculation software, they are available on request. Final calculations should comply with the complete European Technical Approval (ETA), this approval is also available on request.

Technical Specification

d-D	M6
do	6
hef	30
kN	1.5
L (mm)	55
Min. td	50
Ring ø	12
tfix	10
Type	6/10

Technical Drawing

