



FISCHER Bolt type FBN II Steel Zinc plated 6/30 (6X75)

Article number	63324.060.030
Brand	-
UBB	500504267120
UNSPSC	31162101
EAN	4048962070255
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M6
Length	75 mm
Material	Steel
Approval	ETA Option 7
Surface treatment	Zinc plated
Thread	Metric thread
Type no.	FBN II

Info

do = Nominal diameter of drill
bit.tfix = Grip
range.hef = Effective anchorage
depth.Min. td = Recommended
drilling depth.kN = Load in kN.The
allowable load is valid for one single
anchor, at cracked concrete (tensile
zone) with concrete class C20/25, incl.
partial safety factor $\gamma_f = 1,4$ and if the
Scr, N and Ccr, N are taken in to
account.When reduction on spacing
and edge distance take place a re-
calculation of forces

Standards

should be carried out by making use of the technical guide or calculation software, they are available on request. Final calculations should comply with the complete European Technical Approval (ETA), this approval is also available on request.

Technical Specification

d-D	M6
do	6
hef	30
kN	1.5
L (mm)	75
Min. td	70
Ring ø	12
tfix	30
Type	6/30

Technical Drawing

