

FISCHER Adjustable fixing
Plastic Nylon (polyamide) S
10-J 75 S



Article number	63600.060.110
Brand	-
UBB	950372038824
UNSPSC	31162400
EAN	4006209807101
PKG. of 1	Full Box Only

Technical Parameters

Color	Grey
Material	Plastic
Type no.	S10J75S
Info	Adjustable fixing type S10J75S for assembly for wood on stone.With adjustable screw type JS 6 x 110, steel zinc plated, yellow passivated.

Standards

Technical Specification

Assembly depth (min.)	50
Drill depth (min.)	115
Drill ø	10
Plug length	75
Socket	40
Stepless adjustment	0
Type	S 10-J 75 S
Wood thickness (max.)	25