



RAWL Expansion shield anchor bolt projecting version Steel Zinc plated 5.8 M6X25

Article number	65435.060.025
Brand	-
UBB	952351395654
UNSPSC	31162400
EAN	5906675283616
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M6
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread
Info	do = Nominal diameter of drill bit. fs = Washer outside diameter. s (Ws) = Width across flats. Tinst = Tightening torque in Nm. df = Anchor diameter. hmin. = Minimal thickness of concrete member. dd (ho) = Recommended drilling depth. tfix = Grip range. hef = Effective anchorage depth. Smin. = Minimal spacing. Cmin. = Minimal edge distance.

Standards

Technical Specification

Cmin.	53
-------	----

Technical Drawing

d-D	M6
df	6.5
do	12
fs	12.5
hef	45
hmin	100
ho	50
kN	3.33
L (mm)	80
s	10
Smin.	35
tfix(max.)	25
Tinst	6.5

