



**RAWL Expansion shield
anchor bolt projecting
version Steel Zinc plated 5.8
M10X60**

Article number	65435.100.060
Brand	-
UBB	952351396314
UNSPSC	31162400
EAN	5906675283753
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M10
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread
Info	do = Nominal diameter of drill bit.fs = Washer outside diameter.s (Ws) = Width across flats.Tinst = Tightening torque in Nm.df = Anchor diameter.hmin. = Minimal thickness of concrete member.dd (ho) = Recommended drilling depth.tfix = Grip range.hef = Effective anchorage depth.Smin. = Minimal spacing.Cmin. = Minimal edge distance.

Standards

Technical Specification

Cmin.	75
-------	----

Technical Drawing

d-D	M10
df	11
do	16
fs	21
hef	60
hmin	100
ho	65
kN	6.67
L (mm)	135
s	17
Smin.	50
tfix(max.)	60
Tinst	27

