



Self-cutting threaded insert with hexagon socket type 308 2 Steel Case-hardened Zinc plated yellow passivated M4X8

Article No.	71556.040.008
Brand	-
UBB	500505985852
UNSPSC	31162802
EAN	8715494295420
PKG. of 50	Full Box Only

Technical Parameters

d ₁	M4
Length (L) (mm)	8
Info	Drill depth (min.) = Minimum borehole depth for blind holes.
Diameter (d-D)	M4
Material	Steel
Material technical	Case-hardened
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread
Type no.	308 2

Standards

Technical Specification

d ₂	6.5
Drill depth (min.)	10
P (d ₁)	0.70
P (d ₂)	0.80
S (+0,1mm)	3.2

Technical Drawing

