



## Brady HP Perform Poly Tape B30C-2250-569-BR

Article number	7G855968
Brand	-
UBB	500671578051
UNSPSC	46180000
EAN	
PKG. of 1	Full Box Only

### Technical Parameters

Length (L) (mm)	57
Length (mtr)	30.40
Adhesive component	Permanent Acrylic
Basic material	Polyester
Brady material number	B-569
Legend	High Performance Polyester Tape for BBP3X/S3XXX/i3300 Printers
Max. service temp. °C	100 °C
Min. service temp. °C	-40 °C
Print technology	Thermal Transfer
Printer compatibility	BBP30; BBP31; BBP33; BBP35; BBP37
Ribbon series	B30-R10000-WT
Industry	Facility & Safety Identification; General Identification
Color	Brown
Content (pcs)	1
Depth (mm)	215

### Standards

Application method    Facility & Safety  
**FABORY**    Identification;  
    Labelling of  
    Stainless Steel Pipes  
    and Surfaces

Thickness	0.076
Type nr.	B-569
Weight (g)	771
Width (mm)	57