



Brady Pre-printed GHS/ CLP Chemical Labels B30-219-7569-WT 250PC

| | |
|----------------|---------------|
| Article number | 7U100080 |
| Brand | - |
| UBB | 500671605441 |
| UNSPSC | 46180000 |
| EAN | |
| PKG. of 1 | Full Box Only |

Technical Parameters

| | |
|-----------------------|---|
| Color | White |
| Width (mm) | 57 |
| Adhesive component | Permanent Acrylic |
| Basic material | Vinyl |
| Brady material number | B-7569 |
| Legend | Pre-Cut Blank Labels for BBP3X/S3XXX/i3300 Printers |
| Max. service temp. °C | 75 °C |
| Min. service temp. °C | -20 °C |
| Printer compatibility | BBP30; BBP31; BBP33; BBP35; BBP37 |
| Ribbon series | B30-R10000 |
| Industry | Facility & Safety Identification |
| Content (pcs) | 250 |
| Depth (mm) | 212 |
| Finish | Gloss |
| Finish | Glanz |
| Finish | luciu |

Standards

| | |
|--------------------|-------------------------------------|
| Finish | Połysk |
| Finish | Brillo |
| Finish | Lesk |
| Finish | Glanzend |
| Finish | Glossza |
| Finish | Gloss |
| Finish | lesk |
| Application method | Facility & Safety Identification |
| Height (mm) | 98 |
| Length (L) (mm) | 57 |
| Thickness | 0.102 |
| Type nr. | B-7569 |
| Weight (g) | 774 |
| Shape | Rectangle |