



Brady HP Perform Poly Tape B30C-1125-569-RD

Article number	7W531224
Brand	-
UBB	500671581188
UNSPSC	46180000
EAN	
PKG. of 1	Full Box Only

Technical Parameters

Color	Red
Width (mm)	29
Adhesive component	Permanent Acrylic
Basic material	Polyester
Brady material number	B-569
Legend	High Performance Polyester Tape for BBP3X/S3XXX/i3300 Printers
Max. service temp. °C	100 °C
Min. service temp. °C	-40 °C
Print technology	Thermal Transfer
Printer compatibility	BBP30; BBP31; BBP33; BBP35; BBP37
Ribbon series	B30-R10000-WT
Industry	Facility & Safety Identification; General Identification
Content (pcs)	1
Depth (mm)	216
Application method	Facility & Safety Identification; Labelling of

Standards

Stainless Steel Pipes
and Surfaces

FABUKY
OF COURSE
SETTING THE STANDARD

Length (L) (mm) 29

Length (mtr) 30.40

Thickness 0.076

Type nr. B-569

Weight (g) 562