

Dormer Jobber drill A100
DIN 338 HSS Vaporised N26



Article number	7W900682
Brand	-
UBB	500631285458
UNSPSC	23241639
EAN	7320760028889
PKG. of 10	Full Box Only

Technical Parameters

Total length	70
Diameter drill	3.73
Holding system	Cylindrical plug-in axle
Cutting length	39
Cutting material	HSS
Shank shape	Cylindrical
Spiral drill	Yes

Standards