



Bosch Cordless Drill driver GSR 18V-60 FC

Article number	8H120451
Brand	-
UBB	500689206497
UNSPSC	27112700
EAN	3165140963343
PKG. of 1	Full Box Only

Technical Parameters

Width (mm)	443
Cap. in wood (max.) (mm)	38
Cap. in steel (max.) (mm)	13
Screw \varnothing	max. 10 mm
Battery (Ah)	4.0 / 5.0
Battery type	Li-Ion
Cap. in metal (max.) (mm)	13
Depth (mm)	155
Chuck clamping range (mm)	1.5 / 13
No-load speed (1st gear/2nd gear)	0 - 600 / 0 - 1.900
Height (mm)	360
Number of batteries including	3
Torque, max. (Nm)	60
Type nr.	GSR 18V-60 FC
Torque (Nm)	31
Voltage (V)	18
Weight (g)	900
Max RPM	1,900

Standards