



## Brady Icon W009-TRI 050-PE 7PC

Article number	8V838508
Brand	-
UBB	500671776887
UNSPSC	46180000
EAN	
PKG. of 1	Full Box Only

### Technical Parameters

Color	Black/Yellow
Width (mm)	50
Adhesive component	Permanent Acrylic
Basic material	Laminated Polyester
Brady material number	B-7541
Country	EMEA
Legend	ISO Safety Sign - Warning: Biological hazard
Legend language	Global
Max. service temp. °C	110 °C
Min. service temp. °C	-40 °C
PIC description	Warning; Biological hazard
Product regulations	ISO 7010:2011
Sign type	Warning
Content (pcs)	7
Number of holes	0
Finish	Gloss
Finish	Glanz
Finish	luciu
Finish	Połysk

### Standards

Finish	Brillo
Finish	Lesk
Finish	Glanzend
Finish	Glossza
Finish	Gloss
Finish	lesk
Application method	Facility & safety identification
Height (mm)	43
Length (L) (mm)	50
Thickness	0.099
Type nr.	B-7541
Weight (g)	7
Shape	Triangle

**UR COURSE**

BE THE STANDARD  
IN FASTENING SOLUTIONS