

Dormer Jobber drill A108
DIN 338 HSS Vaporised
13.00mm



Article number	9N730094
Brand	-
UBB	500630665965
UNSPSC	23241639
EAN	7320760007808
PKG. of 1	Full Box Only

Technical Parameters

Total length	151
Diameter drill	13
Holding system	Cylindrical plug-in axle
Cutting length	101
Suitable for stainless steel	Yes
Cutting material	HSS
Shank shape	Cylindrical
Spiral drill	Yes

Standards