



Brady Icon W012-TRI 100-PE 3PC

Article number	9P161145
Brand	-
UBB	500671781739
UNSPSC	46180000
EAN	
PKG. of 1	Full Box Only

Technical Parameters

Color	Black/Yellow
Width (mm)	100
Adhesive component	Permanent Acrylic
Basic material	Laminated Polyester
Brady material number	B-7541
Country	EMEA
Legend	ISO Safety Sign - Warning; Electricity
Legend language	Global
Max. service temp. °C	110 °C
Min. service temp. °C	-40 °C
PIC description	Warning; Electricity
Product regulations	ISO 7010
Sign type	Warning
Content (pcs)	3
Number of holes	0
Finish	Gloss
Finish	Glanz
Finish	luciu
Finish	Połysk
Finish	Brillo
Finish	Lesk

Standards

Finish	Glanzend
Finish	Glossza
Finish	Gloss
Finish	lesk
Application method	Facility & safety identification
Height (mm)	87
Length (L) (mm)	100
Thickness	0.099
Type nr.	B-7541
Weight (g)	8
Shape	Triangle

UR COURSE

BE THE STANDARD
IN FASTENING SOLUTIONS