



Brady Tape Vinyl B85-200X15M-595-BK

| | |
|----------------|---------------|
| Article number | 9Y892135 |
| Brand | - |
| UBB | 500671510633 |
| UNSPSC | 46180000 |
| EAN | |
| PKG. of 1 | Full Box Only |

Technical Parameters

| | |
|-----------------------|---|
| Color | Black |
| Width (mm) | 200 |
| Adhesive component | Permanent Acrylic |
| Basic material | Vinyl |
| Brady material number | B-595 |
| Legend | BBP85 Tape - Vinyl 200 mm Black |
| Max. service temp. °C | 82 °C |
| Min. service temp. °C | -40 °C |
| Print technology | Thermal Transfer |
| Printer compatibility | BBP85; PowerMark |
| Ribbon series | B85-R-220x60-BK |
| Industry | Beverage processing;Buildings identification;Chemical;Construction;Education;Energy utilities;Food processing;Government;Healthcare;Manufacturing;Maritime;Mining;Oil & gas;Process;Pulp & paper;Tourism & recreation;Warehouse & logistics |
| Content (pcs) | 1 |

Standards

| | |
|--------------------|----------------------------------|
| Depth (mm) | 390 |
| Finish | Gloss |
| Finish | Glanz |
| Finish | luciu |
| Finish | Połysk |
| Finish | Brillo |
| Finish | Lesk |
| Finish | Glanzend |
| Finish | Glossza |
| Finish | Gloss |
| Finish | lesk |
| Application method | Facility & Safety Identification |
| Length (L) (mm) | 200 |
| Length (mtr) | 15 |
| Thickness | 0.102 |
| Type nr. | B-595 |
| Weight (g) | 1454 |


 THE STANDARD
 IN FASTENING SOLUTIONS

UR COURSE