



## Circular saw blade external dm 315 mm no. of teeth 20 WZ bore 30 mm cut width 3.

Article number	B4960.640.701
Brand	-
UBB	500505014158
UNSPSC	23231200
EAN	3165140194808
PKG. of 1	Full Box Only

### Technical Parameters

Max. number of revolutions	5000
Saw blade diameter	315
Suitable for plastic	No
Suitable for metal	No
Bore diameter	30
Suitable for wood	Yes
Cutting width	3.2
Number of teeth	20
Thickness saw blade	366
Model	Construct Wood

### Standards