



## Bosch Lip & spur drill 12X85 MM

Article number	B4974.120.085
Brand	-
UBB	500577123127
UNSPSC	23241639
EAN	3165140059152
PKG. of 1	Full Box Only

### Technical Parameters

Total length	151
Diameter drill	12
Shaft diameter	10
Holding system	Cylindrical plug-in axle
Cutting length	96
Suitable for stainless steel	No
With centre drill	No
Suitable for plastic	No
Suitable for steel	No
Suitable for concrete	No
Suitable for ceramics	No
Suitable for cast iron	No
Suitable for wood	Yes
Suitable for nonferrous metals	No
Suitable for stone	No
Suitable for glass	No
Double sided drill	No
Plug-in axle with flat end	Yes
Suitable for reborring	No

### Standards

With cooling channel No

Suitable for tiles No

Spiral drill Yes

With quick-lock No