



**TOKU RATCHETS TP  
MR-2310B 3/8**

|                |               |
|----------------|---------------|
| Article number | E2053.000.111 |
| Brand          | -             |
| UBB            | 500503774365  |
| UNSPSC         | 27111753      |
| EAN            | 8717981000234 |
| PKG. of 1      | Full Box Only |

**Technical Parameters**

|                           |            |
|---------------------------|------------|
| Max. operation pressure   | 6.3        |
| Tool insertion            | 3/8 inch   |
| Idle rotational speed     | 175        |
| Air inlet device-sided    | R 1/4 inch |
| Max. loosening torque     | 78         |
| Max. tightening torque    | 78         |
| Ratcheting model          | Yes        |
| Max. thread size (metric) | 12         |
| Air volume required       | 360        |

**Standards**