



**TOKU RATCHETS MR-2410B
1/2**

Article number	E2053.000.115
Brand	-
UBB	203122728579
UNSPSC	27111753
EAN	8717981000241
PKG. of 1	Full Box Only

Technical Parameters

Max. operation pressure	6.3
Tool insertion	1/2 inch
Idle rotational speed	175
Air inlet device-sided	R 1/4 inch
Max. loosening torque	78
Ratcheting model	Yes
Max. thread size (metric)	12
Air volume required	360

Standards