



**TOKU DRILLING MACH
MD3312B 3/8X24UNF LR**

Article number	E2056.000.110
Brand	-
UBB	242230032524
UNSPSC	27112713
EAN	8717981000111
PKG. of 1	Full Box Only

Technical Parameters

Construction	Angled
Drill chuck span	9.5 - 9.5
Drill diameter in steel	10
Idle rotational speed	1900
Air inlet device-sided	R 1/4 inch
Air volume required	360

Standards