



RR RATCHETS RRW-2403 3/8 68NM

Article number	E2077.000.110
Brand	-
UBB	500504319442
UNSPSC	27111753
EAN	8717981000593
PKG. of 1	Full Box Only

Technical Parameters

Max. operation pressure	6.3
Tool insertion	3/8 inch
Idle rotational speed	150
Air inlet device-sided	R 1/4 inch
Max. loosening torque	68
Max. tightening torque	68
Ratcheting model	Yes
Max. thread size (metric)	12
Air volume required	360

Standards