



Pullers 20-3+ clamp depth 200 mm clamping width 250 mm 8.5 t KUKKO

Article number	E9019.020.003
Brand	-
UBB	500504774265
UNSPSC	27111712
EAN	4021176645198
PKG. of 1	Full Box Only

Technical Parameters

Model	Other
Wrench width	27
Max. tensile force	8.5
Number of hooks	2
Reversible arms	Yes
Clamping reach	200
Depth of hooked foot	200
Clamping spread (internal pulling)	180 - 180
Max. clamping spread (external pulling)	250
With quick adjustment	Yes

Standards