



Pullers 20-10+ clamp depth 100 mm clamping width 120 mm 4.5 t KUKKO

Article number	E9019.020.010
Brand	-
UBB	500504773929
UNSPSC	27111712
EAN	4021176644856
PKG. of 1	Full Box Only

Technical Parameters

Model	Other
Wrench width	17
Max. tensile force	4.5
Number of hooks	2
Reversible arms	Yes
Clamping reach	100
Depth of hooked foot	100
Clamping spread (internal pulling)	70 - 70
Max. clamping spread (external pulling)	120
With quick adjustment	Yes

Standards