

Fabory Jobber drill conical
MK2 DIN 345 RN HSS Black
18,0 MM



Article number	F0129.180.001
Brand	-
UBB	240201031723
UNSPSC	23241639
EAN	8715494648615
PKG. of 1	Full Box Only

Technical Parameters

Total length	228
Diameter drill	18
Holding system	Conical plug-in axle
Cutting length	140
Suitable for steel	Yes
Cutting material	HSS
Tip angle	118
Shank shape	Morse taper
Cutting direction	Right
Spiral drill	Yes

Standards