


Fabory Slot drill short N DIN 327 D HSS-EC08 Blanc 14,0 MM



Article No.	F0463.140.001
Brand	-
UBB	240203113461
UNSPSC	27110000
EAN	
PKG. of 1	Full Box Only

Technical Parameters

Basic material	HSS-EC08
d ₁	14
d ₂	12
Diameter (mm)	14
Coating	Blanc
Useful length	16
L ₁	73
L ₂	16
Total length (mm)	73
Shank size (mm)	12
Type	N
z	2
Info	Short model, two cutting edges. Cylindrical shank with clamping flat (Weldon). Flute with 30° right spiral.

Standards

DIN	327D
-----	------

Technical Specification

Technical Drawing

