

Stahlwille Torque wrenches 721 /30



Article number	G0601.000.030
Brand	-
UBB	203122428196
UNSPSC	27111715
EAN	4018754031955
PKG. of 1	Full Box Only

Technical Parameters

Connection type	ratchet
Driving	1/2
Reach (Nm)	60-300 NM
Torque type	mechanical
Type nr.	721
Version (torque)	click

Standards

Info	<p>Torque Wrenches with dual “stop” signal and cut-out, rapid adjustment, dual scale Nm/ft.lb. and long service life. Robust steel tube protects all working parts; even if misused, i.e. attempting to free seized metal fasteners, the measuring element remains stress free. Recalibration--without dismantling--with the aid of checking gauges No. 798, No. 799 or No. 7707 W. Guaranteed accuracy $\pm 4\%$. With certificate.</p>
------	---