



Stahlwille Torque wrenches 721/20/4 721/20/4

| | |
|----------------|---------------|
| Article number | G0601.721.204 |
| Brand | - |
| UBB | 500627652141 |
| UNSPSC | 27111715 |
| EAN | 4018754219490 |
| PKG. of 1 | Full Box Only |

Technical Parameters

| | |
|-------------------|-----------|
| Width (mm) | 558 |
| Drive size | 1/2 |
| Height (mm) | 67 |
| Non spark | No |
| Total length (mm) | 75 |
| Range | 40-200 NM |
| Type nr. | 721/20/4 |

Info

Torque Wrenches with dual "stop" signal and cut-out, rapid adjustment, dual scale Nm/ft.lb. and long service life. Robust steel tube protects all working parts; even if misused, i.e. attempting to free seized metal fasteners, the measuring element remains stress free. Recalibration--without dismantling--with the aid of checking gauges No. 798, No. 799 or No. 7707 W. Guaranteed accuracy $\pm 4\%$. With certificate.

Standards